

# How the technology of flexographic plates affects flexo discontinuity

The extent of the flexo discontinuity depends primarily on the technology of the flexographic plate. Two plate types are commonly used: Kodak Flexcel NX plates and Laser Ablative Mask System (LAMS) plates. The properties of these plates that affect color response and the behavior of ColorFlow software are described below. For more information about these plates, see the technical reference material provided by their manufacturers.

- [Kodak Flexcel NX plates](#)
- [Laser Ablative Mask System \(LAMS\) plates](#)